

# Alizé 1.7™ INFRARED CAMERA



The Alizé 1.7 is a high-end, scientific grade, 640 x 512 pixels resolution, InGaAs camera that marries performance with reliability. It has low noise levels, high efficiency, and a rapid frame rate compatible with an external trigger. This is made possible by a combination of state-of-the-art control electronics and a four stage thermoelectric cooler (TEC) which can maintain an operating temperature as low as -50 °C. The TEC, in turn, uses forced air cooling which requires none of the maintenance of a water or liquid nitrogen chilled unit.


The Alizé 1.7 is amongst the most cost-effective high-end InGaAs cameras on the market.

## TECHNICAL SPECIFICATIONS

	Alizé 1.7v			Alizé 1.7s		
Focal plane array (FPA)	InGaAs			InGaAs		
FPA size (px)	640 x 512			640 x 512		
Pixel size (µm)	15			15		
Spectral range (QE > 10%)	0.51 - 1.71 µm at 25 °C 0.46 - 1.66 µm at -50 °C			0.95 - 1.70 µm at 25 °C 0.91 - 1.64 µm at -50 °C		
FPA operating temperature	-50 °C			-50 °C		
Dark current (sensor at -50 °C)	Target at 21 °C: < 600 (Typ. ~ 500) e <sup>-</sup> /px/s			Target at 21 °C: < 600 e <sup>-</sup> /px/s		
	High	Med	Low	High	Med	Low
Gain setting (e <sup>-</sup> /adu)	2.8	28	130	2.2	7.4	89
Typical readout noise (e <sup>-</sup> )	50	150	800	35	75	350
Full well capacity (ke <sup>-</sup> )	12	800	3500	27	110	1400
Readout modes	CDS	ITR	ITR	ITR, IWR, CDS		
Digitization (bits)	13	15	15	14		
Frame rate in CameraLink™ (fps)	90	190	190	Up to 240 full frame 1900 for a 64x64 px ROI		
Frame rate in USB 3.0 (fps)	185			Up to 250 full frame 1900 for a 128x128 px ROI		
Peak responsivity	1.1 A/W at 1660 nm			1.0 A/W at 1550 nm		
Quantum efficiency	> 70% 0.95 - 1.67 µm at 25 °C > 70% 0.89 - 1.62 µm at -50 °C			> 70% 1.00 - 1.65 µm at 25 °C > 70% 0.96 - 1.59 µm at -50 °C		
Operability (typical)	> 99%			> 99%		
Integration time range	1 µs to 19 minutes (low gain)			1 µs to 19 minutes (low gain)		
Cooling	TEC 4 stages, forced air			TEC 4 stages, forced air		
Cooldown time	< 10 minutes			< 10 minutes		
Ambient temperature range	10 °C to 35 °C			10 °C to 30 °C		
Cold shield	f#/1.4			f#/1.4		
Software	PC (Windows10 - 64-bits) with PHySpec™ control and analysis software					
Computer interface	CameraLink™ or USB 3.0			CameraLink™ or USB 3.0		
External control	Upon Request			Upon Request		
Power consumption on 12V DC (W)	39 (typ. 23)			33 (typ. 20)		
Dimensions	169 mm x 130 mm x 97.25 mm			169 mm x 130 mm x 97.25 mm		
Weight	2.6 kg			2.6 kg		
Certification	CE			CE		

## MAIN ADVANTAGES OF TE COOLED AIR SYSTEM:


- » Compact
- » Highly reliable
- » Long lifetime
- » No maintenance
- » Low dark current
- » Low readout noise



○ Alizé 1.7v

○ Alizé 1.7s

Quantum efficiency presented at 25°C.  
The cut-off wavelength shifts towards the blue by ~ 7nm for every 10 °C of cooling.



Schematic of a thermoelectric device where the Peltier effect is used to generate heat flow between two materials.